



TXA213N

Dimmer 3 channels 300W

Technical characteristics

Architecture

Bus system KNX

Controls and indicators

Indicator lamp yes

Main electrical features

Frequency 50/60 Hz

Power

Incandescent bulb power 20 / 900 W

Total power loss under IN 5.8 W

Connection

Connection cross-sect. flexible conductor 0,75 / 2,5mm²

Connection cross-sect. rigid cable 0,75 / 2.5mm²

Type of load universal

Type of connection quick connect

Use conditions

Operating temperature 0...45 °C