


TXA215



Dimmer 1 channel 1000W

Technical characteristics

Architecture

Bus system	KNX
Fixing mode	Din-Rail

Controls and indicators

Indicator lamp	yes
----------------	-----

Main electrical features

Frequency	50/60 Hz
-----------	----------

Power

Incandescent bulb power	20 / 1000 W
Total power loss under IN	10 W

Materials

Colour	stone grey
--------	------------

Connection

Type of load	universal
--------------	-----------

Safety

Protection index IP	IP20
---------------------	------

Use conditions

Operating temperature	0...45 °C
-----------------------	-----------