



TXA215



## Dimmer 1 channel 1000W

### Technical characteristics

#### Architecture

Bus system KNX

#### Controls and indicators

Indicator lamp yes

#### Main electrical features

Frequency 50/60 Hz

#### Power

Incandescent bulb power 20 / 1000 W

Total power loss under IN 10 W

#### Connection

Connection cross-sect. flexible conductor 0,75 / 2,5mm<sup>2</sup>

Connection cross-sect. rigid cable 0,75 / 2.5mm<sup>2</sup>

Type of load universal

Type of connection quick connect

#### Use conditions

Operating temperature 0...45 °C