



TXA215



**IP20**



## Dimmer 1 channel 1000W

### Technical characteristics

#### Architecture

Bus system	KNX
------------	-----

#### Controls and indicators

Indicator lamp	yes
----------------	-----

#### Main electrical features

Frequency	50/60 Hz
-----------	----------

#### Power

Incandescent bulb power	20 / 1000 W
-------------------------	-------------

Total power loss under IN	10 W
---------------------------	------

#### Materials

Colour	stone grey
--------	------------

#### Connection

Connection cross-sect. flexible conductor	0,75 / 2,5mm <sup>2</sup>
---	---------------------------

Connection cross-sect. rigid cable	0,75 / 2.5mm <sup>2</sup>
------------------------------------	---------------------------

Type of load	universal
--------------	-----------

Type of connection	quick connect
--------------------	---------------

#### Safety

Protection index IP	IP20
---------------------	------

#### Use conditions

Operating temperature	0...45 °C
-----------------------	-----------