



Binary input 10 fold, 230V~, modular, KNX

Technical characteristics

Architecture

Bus system EIB

Dimensions

Depth of installed product 60 mm
Height of installed product 90 mm
Width of installed product 106 mm

Power

Total power loss under IN 0.5 W

Materials

Colour stone grey

Installation, mounting

Mounting type din-Rail

Connection

Connection cross-sect. flexible conductor 0,75 / 2,5mm²
Connection cross-sect. rigid cable 0,75 / 2.5mm²
Type of connection quick connect
Type of connection with QuickConnect plug-in terminals

Safety

Protection index IP IP20

Use conditions

Operating temperature 0...45 °C