



TXA604D



Output module 4x 16A (C)/230V~, KNX

Technical characteristics

Architecture

Bus system	yes
------------	-----

Controls and indicators

Indicator lamp	yes
----------------	-----

Connectivity

Bus system radio frequent	No
---------------------------	----

Main electrical features

Rated operational voltage Ue	230 V
------------------------------	-------

Frequency	50/60 Hz
-----------	----------

Dimensions

Height	90 mm
--------	-------

Power

Max. power with electronic transfo.	1200 W
-------------------------------------	--------

Materials

Colour	stone grey
--------	------------

Incandescent bulbs control

Max. power with incandescent lamps	2300 W
------------------------------------	--------

Connection

Type of connection	quick connect
--------------------	---------------

Safety

Protection index IP	IP20
---------------------	------

Use conditions

Operating temperature	-5...45 °C
-----------------------	------------