



TXA606B

Output module 4x 10A /230V~, KNX

Technical characteristics

Architecture

Fixing mode	REG
-------------	-----

Controls and indicators

Indicator lamp	yes
----------------	-----

Connectivity

Bus system radio frequent	No
---------------------------	----

Main electrical features

Rated operational voltage Ue	230 V
Frequency	50/60 Hz

Dimensions

Height	90 mm
--------	-------

Power

Max. power with electronic transfo.	1000 W
-------------------------------------	--------

Materials

Colour	stone grey
--------	------------

Incandescent bulbs control

Max. power with incandescent lamps	1200 W
------------------------------------	--------

Connection

Connection cross-sect. flexible conductor	0,75 / 2,5mm ²
Connection cross-sect. rigid cable	0,75 / 2.5mm ²
Type of connection	quick connect
Type of connection	with QuickConnect plug-in terminals

Safety

Protection index IP	IP20
---------------------	------

Use conditions

Operating temperature	-5...45 °C
-----------------------	------------