



TXA606B



## Output module 4x 10A /230V~, KNX

### Technical Characteristics

#### Architecture

Bus system yes

Fixing mode REG

#### Functions

Function with positioning function for blind and lamella position  
with safety functions e.g. for wind, rain, alarm  
with sun shade function

#### Controls and indicators

Indicator lamp yes

#### Connectivity

Bus system radio frequent No

#### Main electrical features

Rated operational voltage  $U_e$  230 V

Frequency 50/60 Hz

Rated current 10 A

#### Dimensions

Height 90 mm

#### Power

Max. power with electronic transfo. 1000 W

#### Capacity

Breaking capacity 10A 250V AC1

#### Capacity

Number of modules 4

#### Materials

Colour stone grey

#### Fluorescent bulbs control

Max. power fluo. duo lamp comp. series 15 x 36 W

#### Incandescent bulbs control

Max. power with incandescent lamps 1200 W

#### Connection

Connection cross-sect. flexible conductor 0,75 / 2,5mm<sup>2</sup>

Connection cross-sect. rigid cable 0,75 / 2.5mm<sup>2</sup>

Type of connection quick connect

Type of contacts 6NO

Type of connection with QuickConnect plug-in terminals

#### Settings

Setting Switching time on change of direction is preset

#### Safety

---

Protection index IP

IP20

---

**Use conditions**

Operating temperature

-5...45 °C