




TXA606D



## Output module 6x 16A (C)/230V~, KNX

### Technical characteristics

#### Architecture

Bus system yes

#### Functions

Function with positioning function for blind and lamella position ; with safety functions e.g. for wind, rain, alarm ; with sun shade function

#### Controls and indicators

Indicator lamp yes

#### Connectivity

Bus system radio frequent No

#### Main electrical features

Rated operational voltage Ue 230 V

Frequency 50/60 Hz

#### Dimensions

Height 90 mm

#### Power

Max. power with electronic transfo. 1200 W

#### Materials

Colour stone grey

#### Incandescent bulbs control

Max. power with incandescent lamps 2300 W

#### Connection

Connection cross-sect. flexible conductor 0,75 / 2,5mm<sup>2</sup>

Connection cross-sect. rigid cable 0,75 / 2,5mm<sup>2</sup>

Type of load C-Load

Type of connection quick connect

Type of contacts 6NO

Type of connection with QuickConnect plug-in terminals

#### Settings

Setting Switching time on change of direction is preset

#### Safety

Protection index IP IP20

**Use conditions**

---

Operating temperature

-5...45 °C