



TXA606D



Output module 6x 16A (C)/230V~, KNX

Technical characteristics

Architecture

Fixing mode REG

Controls and indicators

Indicator lamp yes

Connectivity

Bus system radio frequent No

Main electrical features

Rated operational voltage U_e 230 V

Frequency 50/60 Hz

Dimensions

Height 90 mm

Power

Max. power with electronic transfo. 1200 W

Materials

Colour stone grey

Incandescent bulbs control

Max. power with incandescent lamps 2300 W

Safety

Protection index IP IP20

Use conditions

Operating temperature -5...45 °C