



TXA606D



Output module 6x 16A (C)/230V~, KNX

Technical characteristics

Architecture

Bus system yes

Functions

Function with positioning function for blind and lamella position ; with safety functions e.g. for wind, rain, alarm ; with sun shade function

Controls and indicators

Indicator lamp yes

Connectivity

Bus system radio frequent No

Main electrical features

Rated operational voltage U_e 230 V

Frequency 50/60 Hz

Dimensions

Height 90 mm

Power

Max. power with electronic transfo. 1200 W

Incandescent bulbs control

Max. power with incandescent lamps 2300 W

Connection

Connection cross-sect. flexible conductor 0,75 / 2,5mm²

Connection cross-sect. rigid cable 0,75 / 2.5mm²

Type of load C-Load

Type of connection quick connect

Type of contacts 6NO

Type of connection with QuickConnect plug-in terminals

Settings

Setting Switching time on change of direction is preset

Use conditions

Operating temperature -5...45 °C