


TXA608D



## Output module 8x 16A (C)/230V~, KNX

### Technical characteristics

#### Architecture

Fixing mode REG

#### Controls and indicators

Indicator lamp yes

#### Connectivity

Bus system radio frequent No

#### Main electrical features

Rated operational voltage Ue 230 V

Frequency 50/60 Hz

#### Dimensions

Height 90 mm

#### Power

Max. power with electronic transfo. 1200 W

#### Materials

Colour stone grey

#### Incandescent bulbs control

Max. power with incandescent lamps 2300 W

#### Safety

Protection index IP IP20

#### Use conditions

Operating temperature -5...45 °C