



TXA610B



**Output module 10x 10A /230V~, KNX**

**Technical characteristics**

**Architecture**

Fixing mode REG

**Controls and indicators**

Indicator lamp yes

**Connectivity**

Bus system radio frequent No

**Main electrical features**

Rated operational voltage Ue 230 V

Frequency 50/60 Hz

**Dimensions**

Height 90 mm

**Power**

Max. power with electronic transfo. 1000 W

Total power loss under IN 0.7 W

**Materials**

Colour stone grey

**Fluorescent bulbs control**

Max. power fluo. duo lamp comp. series 15 x 36 W

**Incandescent bulbs control**

Max. power with incandescent lamps 1200 W

**Safety**

Protection index IP IP20

**Use conditions**

Operating temperature -5...45 °C