



TXA610B

## Output module 10x 10A /230V~, KNX

### Technical characteristics

#### Architecture

Fixing mode	REG
-------------	-----

#### Controls and indicators

Indicator lamp	yes
----------------	-----

#### Connectivity

Bus system radio frequent	No
---------------------------	----

#### Main electrical features

Rated operational voltage Ue	230 V
Frequency	50/60 Hz

#### Dimensions

Height	90 mm
--------	-------

#### Power

Max. power with electronic transfo.	1000 W
Total power loss under IN	0.7 W

#### Materials

Colour	stone grey
--------	------------

#### Incandescent bulbs control

Max. power with incandescent lamps	1200 W
------------------------------------	--------

#### Connection

Connection cross-sect. flexible conductor	0,75 / 2,5mm <sup>2</sup>
Connection cross-sect. rigid cable	0,75 / 2.5mm <sup>2</sup>
Type of connection	quick connect
Type of connection	with QuickConnect plug-in terminals

#### Safety

Protection index IP	IP20
---------------------	------

#### Use conditions

Operating temperature	-5...45 °C
-----------------------	------------