



TXA610D



## Output module 10x 16A (C)/230V~, KNX

### Technical characteristics

#### Architecture

Bus system	yes
------------	-----

#### Controls and indicators

Indicator lamp	yes
----------------	-----

#### Connectivity

Bus system radio frequent	No
---------------------------	----

#### Main electrical features

Rated operational voltage Ue	230 V
Frequency	50/60 Hz

#### Dimensions

Height	90 mm
--------	-------

#### Power

Max. power with electronic transfo.	1200 W
Total power loss under IN	1.5 W
Power dissipation per coil	0.15 W

#### Materials

Colour	stone grey
--------	------------

#### Incandescent bulbs control

Max. power with incandescent lamps	2300 W
------------------------------------	--------

#### Connection

Type of connection	quick connect
--------------------	---------------

#### Safety

Protection index IP	IP20
---------------------	------

#### Use conditions

Operating temperature	-5...45 °C
-----------------------	------------