



TXA663A

DIMMER 3 CHANNELS 300W NE

Technical characteristics

Architecture

Fixing mode REG

Controls and indicators

Indicator lamp yes

Connectivity

Bus system radio frequent No

Main electrical features

Frequency 50/60 Hz

Fuse

Fuse short-circuit and overload proof (electronic fuse),
overheating protection (display using LEDs)

Power

Incandescent bulb power 900 W

Total power loss under IN 770 mW

Power dissipation per coil 430 mW

Materials

Colour light grey

Connection

Connection cross-sect. rigid cable 0,75 / 2.5mm²

Type of load universal

Type of connection quick connect

Type of connection with QuickConnect plug-in terminals

Equipment

Dimming principle phase cut-on or cut-off according to load type, self-learning

Safety

Protection index IP IP20

Use conditions

Operating temperature -5...45 °C