



TXB601B



Output module 1x 10A /230V~, flush mounted, KNX

Technical characteristics

Controls and indicators

Indicator lamp yes

Connectivity

Bus system radio frequent No

Main electrical features

Rated operational voltage U_e 230 V

Dimensions

Height 44 mm

Height of installed product 44 mm

Dimensions (LLxwwxhh) 44x43x22 mm

Power

Max. power with electronic transfo. 600 W

Total power loss under IN 0.6 W

Fluorescent bulbs control

Max. power fluo. duo lamp comp. series 6 x 58W

Incandescent bulbs control

Max. power with incandescent lamps 600 W

Connection

Connection cross-sect. flexible conductor 0,5 / 2,5mm²

Connection cross-sect. rigid cable 0,5 / 2,5mm²

Number of contacts 1

Type of contacts 1NO

Type of connection with screw terminals

Use conditions

Operating temperature -5...45 °C