



TXB601B



**Output module 1x 10A /230V~, flush mounted, KNX**

**Technical characteristics**

**Controls and indicators**

Indicator lamp yes

**Connectivity**

Bus system radio frequent No

**Main electrical features**

Rated operational voltage Ue 230 V

**Dimensions**

Height 44 mm

Height of installed product 44 mm

Dimensions (LLxwxhh) 44x43x22 mm

**Power**

Max. power with electronic transfo. 600 W

Total power loss under IN 0.6 W

**Fluorescent bulbs control**

Max. power fluo. duo lamp comp. series 6 x 58W

**Incandescent bulbs control**

Max. power with incandescent lamps 600 W

**Connection**

Connection cross-sect. flexible conductor 0,5 / 2,5mm<sup>2</sup>

Connection cross-sect. rigid cable 0,5 / 2,5mm<sup>2</sup>

Type of connection with screw

Number of contacts 1

Type of contacts 1NO

Type of connection with screw terminals

**Use conditions**

Operating temperature -5...45 °C