



TXB602F



## Output module 2x 6A /230V~, flush mounted, KNX

### Technical characteristics

#### Architecture

Bus system	yes
Number of blinds/shutters outputs	1
Fixing mode	flush-mounting

#### Controls and indicators

Indicator lamp	yes
----------------	-----

#### Connectivity

Bus system radio frequent	No
---------------------------	----

#### Main electrical features

Rated operational voltage Ue	230 V
------------------------------	-------

#### Dimensions

Height	44 mm
Height of installed product	44 mm
Dimensions (LLxwxh)	44 x 43 x 22 mm

#### Power

Max. power with electronic transfo.	500 W
Total power loss under IN	0.5 W

#### Materials

Colour	light grey
--------	------------

#### Fluorescent bulbs control

Max. power fluo. duo lamp comp. series	6 x 48W
--	---------

#### Incandescent bulbs control

Max. power with incandescent lamps	500 W
------------------------------------	-------

#### Connection

Type of connection	with screw
Number of contacts	2
Type of connection	with screw terminals

#### Safety

Protection index IP	IP20
---------------------	------

#### Use conditions

Operating temperature	-5...45 °C
-----------------------	------------