



TXB692F



Output module 2x 6A /230V~, 2 inputs, flush mounted, KNX

Technical characteristics

Architecture

Bus system	yes
Number of blinds/shutters outputs	1

Functions

Function	with positioning function for blind and lamella position ; with safety functions e.g. for wind, rain, alarm ; binary input functions: Switching, dimming, blind, value transmitter, scene, priority, timer operation, subplate
----------	--

Controls and indicators

Indicator lamp	yes
----------------	-----

Connectivity

Bus system radio frequent	No
---------------------------	----

Main electrical features

Rated operational voltage Ue	230 V
Type of supply voltage	DC

Dimensions

Height	44 mm
Height of installed product	44 mm
Dimensions (LLxwxh)	44 x 43 x 22 mm

Power

Max. power with electronic transfo.	500 W
Contact rating with 230 V in AC1	1380 W
Total power loss under IN	0.5 W

Fluorescent bulbs control

Max. power fluo. duo lamp comp. series	6 x 48W
--	---------

Incandescent bulbs control

Max. power with incandescent lamps	500 W
------------------------------------	-------

Connection

Connection cross-sect. flexible conductor	0,75 / 2,5mm ²
Connection cross-sect. rigid cable	0,75 / 2.5mm ²
Type of connection	with screw
Number of contacts	2
Type of connection	with screw terminals

Settings

Setting

Switching time on change of direction is preset

Use conditions

Operating temperature

-5...45 °C