



TXB692F



Output module 2x 6A /230V~, 2 inputs, flush mounted, KNX

Technical characteristics

Architecture

Bus system	yes
Number of blinds/shutters outputs	1
Fixing mode	flush-mounting

Controls and indicators

Indicator lamp	yes
----------------	-----

Connectivity

Bus system radio frequent	No
---------------------------	----

Main electrical features

Rated operational voltage Ue	230 V
Type of supply voltage	DC

Dimensions

Height	44 mm
Height of installed product	44 mm
Dimensions (LLxwxh)	44 x 43 x 22 mm

Power

Max. power with electronic transfo.	500 W
Contact rating with 230 V in AC1	1380 W
Total power loss under IN	0.5 W

Materials

Colour	light grey
--------	------------

Fluorescent bulbs control

Max. power fluo. duo lamp comp. series	6 x 48W
--	---------

Incandescent bulbs control

Max. power with incandescent lamps	500 W
------------------------------------	-------

Connection

Type of connection	with screw
Number of contacts	2
Type of connection	with screw terminals

Safety

Protection index IP	IP20
---------------------	------

Use conditions

Operating temperature

-5...45 °C