



TXM616D



**Output module 16x 16A (C)/230V~, KNX**

**Technical characteristics**

**Architecture**

Fixing mode REG

**Controls and indicators**

Indicator lamp yes

**Connectivity**

Bus system radio frequent No

**Main electrical features**

Rated operational voltage  $U_e$  230 V

Frequency 50/60 Hz

**Dimensions**

Height 90 mm

**Power**

Max. power with electronic transfo. 1500 W

Total power loss under IN 1.3 W

Power dissipation per coil 150 mW

**Materials**

Colour light grey

**Incandescent bulbs control**

Max. power with incandescent lamps 2300 W

**Connection**

Type of connection with screw terminals

**Safety**

Protection index IP IP20

**Use conditions**

Operating temperature -5...45 °C