



TXM616D



Output module 16x 16A (C)/230V~, KNX

Technical characteristics

Architecture

Bus system	yes
------------	-----

Controls and indicators

Indicator lamp	yes
----------------	-----

Connectivity

Bus system radio frequent	No
---------------------------	----

Main electrical features

Rated operational voltage Ue	230 V
------------------------------	-------

Frequency	50/60 Hz
-----------	----------

Dimensions

Height	90 mm
--------	-------

Power

Max. power with electronic transfo.	1500 W
-------------------------------------	--------

Total power loss under IN	1.3 W
---------------------------	-------

Power dissipation per coil	150 mW
----------------------------	--------

Materials

Colour	light grey
--------	------------

Incandescent bulbs control

Max. power with incandescent lamps	2300 W
------------------------------------	--------

Connection

Type of connection	with screw
--------------------	------------

Type of connection	with screw terminals
--------------------	----------------------

Safety

Protection index IP	IP20
---------------------	------

Use conditions

Operating temperature	-5...45 °C
-----------------------	------------