



TYA604B



## Output module 4x 10A /230V~, KNX

### Technical characteristics

#### Architecture

Fixing mode REG

#### Controls and indicators

Indicator lamp yes

#### Connectivity

Bus system radio frequent No

#### Dimensions

Height 90 mm

Width 70 mm

#### Power

Max. power with electronic transfo. 1000 W

Total power loss under IN 3 W

#### Fluorescent bulbs control

Max. power fluo. duo lamp comp. series 15 x 36 W

#### Incandescent bulbs control

Max. power with incandescent lamps 1200 W

#### Safety

Protection index IP IP20

#### Use conditions

Operating temperature -5...45 °C