



TYA604D



## Output module 4x 16A (C)/230V~, KNX

### Technical characteristics

#### Architecture

Fixing mode REG

#### Controls and indicators

Indicator lamp yes

#### Connectivity

Bus system radio frequent No

#### Main electrical features

Rated operational voltage  $U_e$  230 V

#### Dimensions

Depth 65 mm

Height 90 mm

#### Power

Max. power with electronic transfo. 1200 W

Total power loss under IN 8 W

#### Materials

Colour light grey

#### Fluorescent bulbs control

Max. power fluo. duo lamp comp. series 20 x 36 W

#### Incandescent bulbs control

Max. power with incandescent lamps 2300 W

#### Safety

Protection index IP IP20

#### Use conditions

Operating temperature -5...45 °C