



TYA604D



## Output module 4x 16A (C)/230V~, KNX

### Technical characteristics

#### Architecture

Bus system yes

#### Functions

Function with positioning function for blind and lamella position ; with safety functions e.g. for wind, rain, alarm ; with sun shade function

#### Controls and indicators

Indicator lamp yes

#### Connectivity

Bus system radio frequent No

#### Main electrical features

Rated operational voltage  $U_e$  230 V

#### Dimensions

Depth 65 mm

Height 90 mm

#### Power

Max. power with electronic transfo. 1200 W

Total power loss under IN 8 W

#### Fluorescent bulbs control

Max. power fluo. duo lamp comp. series 20 x 36 W

#### Incandescent bulbs control

Max. power with incandescent lamps 2300 W

#### Connection

Connection cross-sect. flexible conductor 0,75 / 2,5mm<sup>2</sup>

Connection cross-sect. rigid cable 0,75 / 2.5mm<sup>2</sup>

Type of load C-Load

Type of connection quick connect

Type of contacts 4NO

Type of connection with QuickConnect plug-in terminals

#### Settings

Setting switching time on change of direction adjustable

#### Use conditions

