



TYA606A



Output module 6x 4A /230V~, KNX

Technical characteristics

Architecture

Fixing mode REG

Controls and indicators

Indicator lamp yes

Connectivity

Bus system radio frequent No

Dimensions

Depth 65 mm

Height 90 mm

Power

Max. power with electronic transfo. 800 W

Total power loss under IN 1 W

Materials

Colour light grey

Fluorescent bulbs control

Max. power fluo. duo lamp comp. series 12 x 36 W

Incandescent bulbs control

Max. power with incandescent lamps 800 W

Safety

Protection index IP IP20

Use conditions

Operating temperature -5...45 °C