



TYA606B



Output module 6x 10A /230V~, KNX

Technical characteristics

Architecture

Fixing mode REG

Controls and indicators

Indicator lamp yes

Connectivity

Bus system radio frequent No

Dimensions

Height 90 mm

Width 70 mm

Power

Max. power with electronic transfo. 1000 W

Total power loss under IN 5 W

Fluorescent bulbs control

Max. power fluo. duo lamp comp. series 15 x 36 W

Incandescent bulbs control

Max. power with incandescent lamps 1200 W

Safety

Protection index IP IP20

Use conditions

Operating temperature -5...45 °C