


TYA606D



Output module 6x 16A (C)/230V~, KNX

Technical characteristics

Architecture

Bus system	yes
------------	-----

Functions

Function	with positioning function for blind and lamella position ; with safety functions e.g. for wind, rain, alarm ; with sun shade function
----------	---

Controls and indicators

Indicator lamp	yes
----------------	-----

Connectivity

Bus system radio frequent	No
---------------------------	----

Main electrical features

Rated operational voltage U _e	230 V
--	-------

Dimensions

Depth	65 mm
Height	90 mm

Power

Max. power with electronic transfo.	1200 W
Total power loss under IN	12 W

Materials

Colour	light grey
--------	------------

Fluorescent bulbs control

Max. power fluo. duo lamp comp. series	20 x 36 W
--	-----------

Incandescent bulbs control

Max. power with incandescent lamps	2300 W
------------------------------------	--------

Connection

Connection cross-sect. flexible conductor	0,75 / 2,5mm ²
Connection cross-sect. rigid cable	0,75 / 2.5mm ²
Type of load	C-Load
Type of connection	quick connect
Type of contacts	6NO
Type of connection	with QuickConnect plug-in terminals

Settings

Setting	switching time on change of direction adjustable
Safety	
Protection index IP	IP20
Use conditions	
Operating temperature	-5...45 °C