



TYA606E



Output 6 -fold 16A C-Load adapted with current monitoring

Technical characteristics

Architecture

Bus system KNX

Functions

Function with operating hours meter

Controls and indicators

Indicator lamp yes

Connectivity

Bus system radio frequent No

Main electrical features

Rated operational voltage Ue 230 V

Frequency 50/60 Hz

Power

Max. power with electronic transfo. 1380 W

Total power loss under IN 6 W

Fluorescent bulbs control

Max. power fluo. duo lamp comp. series 25x18W

Incandescent bulbs control

Max. power with incandescent lamps 2300 W

Connection

Connection cross-sect. flexible conductor 0,75 / 2,5mm²

Connection cross-sect. rigid cable 0,75 / 2.5mm²

Type of load C-Load

Type of connection quick connect

Type of contacts 6NO

Type of connection with plug-in terminals

Use conditions

Operating temperature -5...45 °C