



TYA606E



**Output 6 -fold 16A C-Load adapted with current monitoring**

**Technical characteristics**

**Architecture**

Bus system KNX

**Functions**

Function with operating hours meter

**Controls and indicators**

Indicator lamp yes

**Connectivity**

Bus system radio frequent No

**Main electrical features**

Rated operational voltage Ue 230 V

**Power**

Max. power with electronic transfo. 1380 W

Total power loss under IN 6 W

**Fluorescent bulbs control**

Max. power fluo. duo lamp comp. series 25x18W

**Incandescent bulbs control**

Max. power with incandescent lamps 2300 W

**Connection**

Connection cross-sect. flexible conductor 0,75 / 2,5mm<sup>2</sup>

Connection cross-sect. rigid cable 0,75 / 2.5mm<sup>2</sup>

Type of load C-Load

Type of contacts 6NO

Type of connection with plug-in terminals

**Use conditions**

Operating temperature -5...45 °C