



TYA606E



Output 6 -fold 16A C-Load adapted with current monitoring

Technical characteristics

Architecture

Bus system	KNX
------------	-----

Functions

Function	with operating hours meter
----------	----------------------------

Controls and indicators

Indicator lamp	yes
----------------	-----

Connectivity

Bus system radio frequent	No
---------------------------	----

Main electrical features

Rated operational voltage Ue	230 V
------------------------------	-------

Frequency	50/60 Hz
-----------	----------

Power

Max. power with electronic transfo.	1380 W
-------------------------------------	--------

Total power loss under IN	6 W
---------------------------	-----

Materials

Colour	light grey
--------	------------

Fluorescent bulbs control

Max. power fluo. duo lamp comp. series	25x18W
--	--------

Incandescent bulbs control

Max. power with incandescent lamps	2300 W
------------------------------------	--------

Connection

Connection cross-sect. flexible conductor	0,75 / 2,5mm ²
---	---------------------------

Connection cross-sect. rigid cable	0,75 / 2,5mm ²
------------------------------------	---------------------------

Type of load	C-Load
--------------	--------

Type of connection	quick connect
--------------------	---------------

Type of contacts	6NO
------------------	-----

Safety

Protection index IP	IP20
---------------------	------

Use conditions

Operating temperature	-5...45 °C
-----------------------	------------