


TYA608A



## Output module 8x 4A /230V~, KNX

### Technical characteristics

#### Architecture

Bus system	yes
Fixing mode	REG

#### Functions

Function	with positioning function for blind and lamella position ; with safety functions e.g. for wind, rain, alarm ; with sun shade function
----------	---

#### Controls and indicators

Indicator lamp	yes
----------------	-----

#### Connectivity

Bus system radio frequent	No
---------------------------	----

#### Dimensions

Depth	65 mm
Height	90 mm

#### Power

Max. power with electronic transfo.	800 W
Total power loss under IN	2 W

#### Materials

Colour	light grey
--------	------------

#### Fluorescent bulbs control

Max. power fluo. duo lamp comp. series	12 x 36 W
--	-----------

#### Incandescent bulbs control

Max. power with incandescent lamps	800 W
------------------------------------	-------

#### Connection

Connection cross-sect. flexible conductor	0,75 / 2,5mm <sup>2</sup>
Connection cross-sect. rigid cable	0,75 / 2.5mm <sup>2</sup>
Type of connection	quick connect
Type of contacts	8NO
Type of connection	with QuickConnect plug-in terminals

#### Settings

Setting	switching time on change of direction adjustable
---------	--

#### Safety

Protection index IP

IP20

**Use conditions**

---

Operating temperature

-5...45 °C