


TYA608B



Output module 8x 10A /230V~, KNX

Technical characteristics

Architecture

Bus system	yes
Fixing mode	REG

Functions

Function	with positioning function for blind and lamella position ; with safety functions e.g. for wind, rain, alarm ; with sun shade function
----------	---------------------------------------------------------------------------------------------------------------------------------------

Controls and indicators

Indicator lamp	yes
----------------	-----

Connectivity

Bus system radio frequent	No
---------------------------	----

Dimensions

Height	90 mm
Width	105 mm

Power

Max. power with electronic transfo.	1000 W
Total power loss under IN	6 W

Fluorescent bulbs control

Max. power fluo. duo lamp comp. series	15 x 36 W
----------------------------------------	-----------

Incandescent bulbs control

Max. power with incandescent lamps	1200 W
------------------------------------	--------

Connection

Connection cross-sect. flexible conductor	0,75 / 2,5mm ²
Connection cross-sect. rigid cable	0,75 / 2.5mm ²
Type of connection	quick connect
Type of contacts	8NO
Type of connection	with QuickConnect plug-in terminals

Settings

Setting	switching time on change of direction adjustable
---------	--------------------------------------------------

Safety

Protection index IP	IP20
---------------------	------

Use conditions

