



TYA608B



Output module 8x 10A /230V~, KNX

Technical Characteristics

Bus system	yes
Fixing mode	REG
Function	with positioning function for blind and lamella position with safety functions e.g. for wind, rain, alarm with sun shade function
Indicator lamp	yes
Bus system radio frequent	No
Height	90 mm
Width	105 mm
Dimensions (W x H x D)	105 x 90 x 65 mm
Max. power with electronic transfo.	1000 W
Total power loss under IN	6 W
Breaking capacity	10A 250V AC1
Number of modules	6
Max. power fluo. duo lamp comp. series	15 x 36 W
Max. power with incandescent lamps	1200 W
Connection cross-sect. flexible conductor	0,75 / 2,5mm ²
Connection cross-sect. rigid cable	0,75 / 2.5mm ²
Type of connection	quick connect
Type of contacts	8NO
Type of connection	with QuickConnect plug-in terminals
Setting	switching time on change of direction adjustable
Protection index IP	IP20
Operating temperature	-5...45 °C
Designation syntax: Main application	10 A, with auxiliary voltage