


TYA608C



Output module 8x 16A /230V~, KNX

Technical characteristics

Architecture

Bus system	yes
------------	-----

Controls and indicators

Indicator lamp	yes
----------------	-----

Connectivity

Bus system radio frequent	No
---------------------------	----

Dimensions

Depth	65 mm
Height	90 mm

Power

Total power loss under IN	12 W
---------------------------	------

Materials

Colour	light grey
--------	------------

Fluorescent bulbs control

Max. power fluo. duo lamp comp. series	20 x 36 W
--	-----------

Incandescent bulbs control

Max. power with incandescent lamps	2300 W
------------------------------------	--------

Connection

Type of connection	quick connect
--------------------	---------------

Safety

Protection index IP	IP20
---------------------	------

Use conditions

Operating temperature	-5...45 °C
-----------------------	------------