


TYA608D



## Output module 8x 16A (C)/230V~, KNX

### Technical characteristics

#### Architecture

Bus system	yes
Fixing mode	REG

#### Functions

Function	with positioning function for blind and lamella position ; with safety functions e.g. for wind, rain, alarm ; with sun shade function
----------	---

#### Controls and indicators

Indicator lamp	yes
----------------	-----

#### Connectivity

Bus system radio frequent	No
---------------------------	----

#### Main electrical features

Rated operational voltage Ue	230 V
------------------------------	-------

#### Dimensions

Depth	65 mm
Height	90 mm

#### Power

Max. power with electronic transfo.	1200 W
Total power loss under IN	8 W

#### Materials

Colour	light grey
--------	------------

#### Fluorescent bulbs control

Max. power fluo. duo lamp comp. series	20 x 36 W
--	-----------

#### Incandescent bulbs control

Max. power with incandescent lamps	2300 W
------------------------------------	--------

#### Connection

Connection cross-sect. flexible conductor	0,75 / 2,5mm <sup>2</sup>
Connection cross-sect. rigid cable	0,75 / 2.5mm <sup>2</sup>
Type of load	C-Load
Type of connection	quick connect
Type of contacts	8NO
Type of connection	with QuickConnect plug-in terminals

---

**Settings**

Setting switching time on change of direction adjustable

---

**Safety**

Protection index IP IP20

---

**Use conditions**

Operating temperature -5...45 °C