



TYA610A



Output module 10x 4A /230V~, KNX

Technical characteristics

Architecture

Bus system	KNX
Fixing mode	REG

Controls and indicators

Indicator lamp	yes
----------------	-----

Connectivity

Bus system radio frequent	No
---------------------------	----

Dimensions

Depth	65 mm
Height	90 mm

Power

Max. power with electronic transfo.	800 W
Total power loss under IN	0.7 W
Power dissipation per coil	0.15 W

Materials

Colour	light grey
--------	------------

Fluorescent bulbs control

Max. power fluo. duo lamp comp. series	12 x 36 W
--	-----------

Incandescent bulbs control

Max. power with incandescent lamps	800 W
------------------------------------	-------

Safety

Protection index IP	IP20
---------------------	------

Use conditions

Operating temperature	-5...45 °C
-----------------------	------------