



TYA610B



Output module 10x 10A /230V~, KNX

Technical characteristics

Architecture

Fixing mode REG

Controls and indicators

Indicator lamp yes

Connectivity

Bus system radio frequent No

Dimensions

Height 90 mm

Width 105 mm

Power

Max. power with electronic transfo. 1000 W

Total power loss under IN 0.7 W

Power dissipation per coil 0.15 W

Fluorescent bulbs control

Max. power fluo. duo lamp comp. series 15 x 36 W

Incandescent bulbs control

Max. power with incandescent lamps 1200 W

Safety

Protection index IP IP20

Use conditions

Operating temperature -5...45 °C