



TYA610B



Output module 10x 10A /230V~, KNX

Technical characteristics

Architecture

Bus system	yes
------------	-----

Controls and indicators

Indicator lamp	yes
----------------	-----

Connectivity

Bus system radio frequent	No
---------------------------	----

Dimensions

Height	90 mm
Width	105 mm

Power

Max. power with electronic transfo.	1000 W
Total power loss under IN	0.7 W
Power dissipation per coil	0.15 W

Fluorescent bulbs control

Max. power fluo. duo lamp comp. series	15 x 36 W
--	-----------

Incandescent bulbs control

Max. power with incandescent lamps	1200 W
------------------------------------	--------

Connection

Type of connection	quick connect
--------------------	---------------

Safety

Protection index IP	IP20
---------------------	------

Use conditions

Operating temperature	-5...45 °C
-----------------------	------------