



TYA610C



**Output module 10x 16A /230V~, KNX**

**Technical characteristics**

**Architecture**

Fixing mode REG

**Controls and indicators**

Indicator lamp yes

**Connectivity**

Bus system radio frequent No

**Dimensions**

Depth 65 mm

Height 90 mm

**Power**

Total power loss under IN 1.5 W

Power dissipation per coil 0.15 W

**Materials**

Colour light grey

**Fluorescent bulbs control**

Max. power fluo. duo lamp comp. series 20 x 36 W

**Incandescent bulbs control**

Max. power with incandescent lamps 2300 W

**Safety**

Protection index IP IP20

**Use conditions**

Operating temperature -5...45 °C