



TYA610D



**Output module 10x 16A (C)/230V~, KNX**

**Technical characteristics**

**Architecture**

Bus system yes

**Functions**

Function with positioning function for blind and lamella position ; with safety functions e.g. for wind, rain, alarm ; with sun shade function

**Controls and indicators**

Indicator lamp yes

**Connectivity**

Bus system radio frequent No

**Main electrical features**

Rated operational voltage  $U_e$  230 V

**Dimensions**

Depth 65 mm

Height 90 mm

**Power**

Max. power with electronic transfo. 1200 W

Total power loss under IN 1.5 W

**Fluorescent bulbs control**

Max. power fluo. duo lamp comp. series 20 x 36 W

**Incandescent bulbs control**

Max. power with incandescent lamps 2300 W

**Connection**

Connection cross-sect. flexible conductor 0,75 / 2,5mm<sup>2</sup>

Connection cross-sect. rigid cable 0,75 / 2.5mm<sup>2</sup>

Type of load C-Load

Type of connection quick connect

Type of contacts 10NO

Type of connection with QuickConnect plug-in terminals

**Settings**

Setting switching time on change of direction adjustable

**Use conditions**

