



TYA624A

**IP20**

**Shutter module 4x 6A /230V~, KNX**

**Technical characteristics**

**Architecture**

Bus system	KNX
Number of blinds/shutters outputs	4

**Functions**

Function	with sun shade function ; with safety functions e.g. for wind, rain, alarm ; with positioning function for roller shutter position
----------	--

**Controls and indicators**

Indicator lamp	yes
----------------	-----

**Connectivity**

Bus system radio frequent	No
---------------------------	----

**Main electrical features**

Frequency	50/60 Hz
Type of supply voltage	AC

**Dimensions**

Depth	65 mm
Height	90 mm

**Power**

Contact rating with 230 V in AC1	1380 W
Total power loss under IN	2 W

**Materials**

RAL colour	RAL 7035 - Light grey
------------	-----------------------

**Connection**

Connection cross-sect. flexible conductor	0,75 / 2,5mm <sup>2</sup>
Connection cross-sect. rigid cable	0,75 / 2.5mm <sup>2</sup>
Type of connection	quick connect
Number of contacts	4
Type of connection	with QuickConnect plug-in terminals

**Settings**

Setting	switching time on change of direction adjustable
---------	--

**Use conditions**

Operating temperature	-5...45 °C
-----------------------	------------