



TYA624A

IP20

Shutter module 4x 6A /230V~, KNX

Technical characteristics

Architecture

Bus system	KNX
Number of blinds/shutters outputs	4

Functions

Function	with sun shade function ; with safety functions e.g. for wind, rain, alarm ; with positioning function for roller shutter position
----------	--

Controls and indicators

Indicator lamp	yes
----------------	-----

Connectivity

Bus system radio frequent	No
---------------------------	----

Main electrical features

Frequency	50/60 Hz
Type of supply voltage	AC

Dimensions

Depth	65 mm
Height	90 mm

Power

Contact rating with 230 V in AC1	1380 W
Total power loss under IN	2 W

Materials

RAL colour	RAL 7035 - Light grey
------------	-----------------------

Connection

Connection cross-sect. flexible conductor	0,75 / 2,5mm ²
Connection cross-sect. rigid cable	0,75 / 2.5mm ²
Type of connection	quick connect
Number of contacts	4
Type of connection	with QuickConnect plug-in terminals

Settings

Setting	switching time on change of direction adjustable
---------	--

Use conditions

Operating temperature	-5...45 °C
-----------------------	------------