


TYA628A



**IP20**

## Shutter module 8x 6A /230V~, KNX

### Technical characteristics

#### Architecture

Bus system	KNX
Number of blinds/shutters outputs	8

#### Functions

Function	with sun shade function ; with safety functions e.g. for wind, rain, alarm ; with positioning function for roller shutter position
----------	--

#### Controls and indicators

Indicator lamp	yes
----------------	-----

#### Connectivity

Bus system radio frequent	No
---------------------------	----

#### Main electrical features

Frequency	50/60 Hz
Type of supply voltage	AC

#### Dimensions

Depth	65 mm
Height	90 mm

#### Power

Contact rating with 230 V in AC1	1380 W
Total power loss under IN	2 W

#### Materials

Colour	light grey
--------	------------

#### Connection

Connection cross-sect. flexible conductor	0,75 / 2,5mm <sup>2</sup>
Connection cross-sect. rigid cable	0,75 / 2.5mm <sup>2</sup>
Type of connection	quick connect
Number of contacts	8
Type of connection	with QuickConnect plug-in terminals

#### Settings

Setting	switching time on change of direction adjustable
---------	--

#### Safety

Protection index IP	IP20
---------------------	------

#### Use conditions

---

Operating temperature

-5...45 °C