



TYA663AN



Dimmer 3 channels 300W

Technical characteristics

Architecture

Fixing mode REG

Controls and indicators

Indicator lamp yes

Connectivity

Bus system radio frequent No

Main electrical features

Frequency 50/60 Hz

Fuse

Fuse overheating protection (display using LEDs)

Power

Incandescent bulb power 900 W

Connection

Type of load universal

Equipment

Dimming principle phase cut-on or cut-off according to load type, self-learning

Safety

Protection index IP IP20

Use conditions

Operating temperature -5...45 °C