



TYA664AN

## DIMMER 4 CHANNELS 300W WITH PARALLELIZATION

### Technical characteristics

#### Architecture

Fixing mode	REG
-------------	-----

#### Controls and indicators

Indicator lamp	yes
----------------	-----

#### Connectivity

Bus system radio frequent	No
---------------------------	----

#### Main electrical features

Frequency	50/60 Hz
-----------	----------

#### Fuse

Fuse	overheating protection (display using LEDs)
------	---

#### Power

Incandescent bulb power	5 / 300 W
Total power loss under IN	0.35 W
Power dissipation per coil	1 W

#### Power supply

Supply voltage	230 V +10% / -15%
----------------	-------------------

#### Materials

Colour	RAL 7035
--------	----------

#### Incandescent bulbs control

Max. power with incandescent lamps	300 W
------------------------------------	-------

#### Connection

Connection cross-sect. flexible conductor	0,75 / 2,5mm <sup>2</sup>
Connection cross-sect. rigid cable	0,75 / 2.5mm <sup>2</sup>
Type of load	universal
Type of connection	quick connect
Type of connection	with QuickConnect plug-in terminals

#### Equipment

Dimming principle	phase cut-on or cut-off according to load type, self-learning
-------------------	---

#### Safety

Protection index IP	IP20
---------------------	------

#### Use conditions

---

Operating temperature

-5...45 °C