



TYA670D

## Gateway KNX/EIB-DALI, 4 modules

### Technical characteristics

#### Architecture

Bus system	EIB
------------	-----

#### Connectivity

Bus system radio frequent	No
---------------------------	----

#### Main electrical features

Frequency	50/60 Hz
-----------	----------

#### Voltage

Operating voltage	240 V DC
-------------------	----------

#### Dimensions

Depth	70 mm
Height	90 mm
Width	72 mm

#### Power

Power consumed	0.15 W
Total power loss under IN	3 W

#### Materials

Colour	stone grey
RAL colour	RAL 7035 - Light grey
Material	plastic
Type of surface treatment	untreated

#### Connection

Type of load	Dali product
Type of connection	with screw terminals

#### Equipment

Lighting	Setting of 16 effects with up to 16 steps for dynamic lighting control ; Integration of the device into DALI emergency lighting systems conforming to IEC 62386-101 with settings and monitoring of emergency mode
----------	--

#### Safety

Protection index IP	IP30
---------------------	------

#### Use conditions

Operating temperature	5...45 °C
-----------------------	-----------