



TYB602F



Output module 2x 6A /230V~, flush mounted, KNX

Technical characteristics

Architecture

Fixing mode flush-mounting

Controls and indicators

Indicator lamp yes

Connectivity

Bus system radio frequent No

Main electrical features

Rated operational voltage U_e 230 V

Dimensions

Height 44 mm

Height of installed product 44 mm

Dimensions (LLxwxhh) 44 x 43 x 22 mm

Power

Max. power with electronic transfo. 500 W

Total power loss under IN 0.5 W

Materials

Colour light grey

Fluorescent bulbs control

Max. power fluo. duo lamp comp. series 6 x 48W

Incandescent bulbs control

Max. power with incandescent lamps 500 W

Connection

Number of contacts 2

Type of contacts 1NO

Type of connection with screw terminals

Safety

Protection index IP IP20

Use conditions

Operating temperature -5...45 °C