



TYB692F



**Output module 2x 6A /230V~, 2 inputs, flush mounted, KNX**

**Technical characteristics**

**Architecture**

Fixing mode flush-mounting

**Controls and indicators**

Indicator lamp yes

**Connectivity**

Bus system radio frequent No

**Main electrical features**

Rated operational voltage  $U_e$  230 V

**Dimensions**

Height 44 mm

Height of installed product 44 mm

Dimensions (LLxwwxhh) 44 x 43 x 22 mm

**Power**

Max. power with electronic transfo. 500 W

Total power loss under IN 0.5 W

**Materials**

Colour light grey

**Fluorescent bulbs control**

Max. power fluo. duo lamp comp. series 6 x 48W

**Incandescent bulbs control**

Max. power with incandescent lamps 500 W

**Connection**

Number of contacts 2

Type of contacts 1NO

Type of connection with screw terminals

**Safety**

Protection index IP IP20

**Use conditions**

Operating temperature -5...45 °C